

Prompt S / P / SP

Technical Data



Prompt S

Prompt P

Prompt SP

Prompt S / P / SP | Features and Accessories

	Prompt S / P / SP
Audiology	
Signal processing (channels) / Gain/MPO (handles)	8 / 4
Hearing programs	4
SpeechMaster	—
HD Music (presets)	—
TwinPhone¹⁾	—
EchoShield	—
Wireless CROS/BICROS²⁾	—
Directionality (channels)	8
Narrow Directionality¹⁾	—
Directional microphone	—
Spatial SpeechFocus¹⁾	—
SpeechFocus	—
TruEar™	—
Frequency compression	—
Extended bandwidth	—
Feedback cancellation	●
eWindScreen binaural¹⁾	—
eWindScreen™ (steps)	—
Noise Reduction (channels / steps)	—
Speech and noise management (steps)	on / off
SoundSmoothing™ (steps)	—
Directional speech enhancement (steps)	—
Adaptive streaming volume³⁾	—
SoundBrilliance™ ³⁾	—
Sound equalizer (classes)	—
Spatial Configurator¹⁾	—
Span⁴⁾	—
Direction⁵⁾	—
SoundBalance	—
Fitting	
Insitugram	●
Learning (classes) / Data logging	— / ●
Acclimatization manager	—
Tinnitus	
Tinnitus noiser	
Static therapy signal (handles / presets)	—
Ocean Waves therapy signal (presets)	—

Prompt S / P / SP | Features and Accessories

	Prompt S	Prompt P	Prompt SP
Style Specific Features			
Ingress Protection Rating	IP67	—	—
Telecoil	—	●	●
AutoPhone™	—	—	—
Charging contacts	—	—	—
Battery Size	312	13	675
Battery door on/off function	●	●	●
Nanocoated housing	●	●	●
e2e wireless™ 3.0	—	—	—
Audio streaming	—	—	—
User controls coupling via e2e	—	—	—
Wireless programming via ConnexxLink™	—	—	—
Instrument configurations			
Flat cover	—	—	—
Volume wheel	—	—	—
Push button	●	●	●
Rocker switch	—	●	●
Color conversion kit	—	—	—
Battery door – direct audio input	—	○	○
Battery door – child lock	—	—	—
Accessories			
miniPocket	○	○	○
CROS Pure	—	—	—
eCharger	—	—	—
easyPocket™	—	—	—
easyTek	—	—	—
TV Transmitter (req. easyTek)	—	—	—
Transmitter (req. easyTek)	—	—	—
VoiceLink™ (req. easyTek)	—	—	—
App			
MobileFitting App	—	—	—
easyTek App (req. easyTek)	—	—	—
touchControl App	○	○	○

● available ■■■■■ highest feature performance ○ optional — not available

¹⁾ req. bilateral fitting and e2e™ 3.0

²⁾ req. CROS Pure accessory

³⁾ streaming only, req. easyTek™

⁴⁾ req. easyTek & easyTek App, touchControl App or rocker switch

⁵⁾ req. easyTek & easyTek App or touchControl App

Prompt Custom

Technical Data

ITE

ITC

CIC

Prompt Custom | Features and Accessories

	ITE / ITC / CIC
Audiology	
Signal processing ¹⁾ / Gain/MPO ²⁾	8 / 4
Hearing programs	4
SpeechMaster	—
HD Music ³⁾	—
TwinPhone ⁴⁾ 13)	—
EchoShield	—
Wireless CROS/BICROS ⁵⁾	—
Directionality (channels)	—
Narrow Directionality ¹⁾	—
Directional microphone	—
Spatial SpeechFocus ¹⁾	—
SpeechFocus	—
TruEar™	—
Frequency compression	—
Extended bandwidth	—
Feedback cancellation	●
eWindScreen binaural ⁴⁾	—
eWindScreen™ (steps)	—
Noise Reduction (channels / steps)	on / off
Speech and noise management (steps)	—
SoundSmoothing™ (steps)	—
Directional speech enhancement (steps)	—
Adaptive streaming volume ³⁾	—
SoundBrilliance™ ³⁾	—
Sound equalizer (classes)	—
Spatial Configurator ¹⁾	—
Span ⁴⁾	—
Direction ⁵⁾	—
SoundBalance	—
Fitting	
Insitugram	●
Learning (classes) / Data logging	— / ●
Acclimatization manager	—
Tinnitus	
Tinnitus noiser	
Static therapy signal (handels / presets)	—
Ocean Waves therapy signal (presets)	—
Notch therapy	—

Prompt Custom | Features and Accessories

	ITE	ITC	CIC
Style Specific Features			
Ingress Protection Rating	—	—	—
Telecoil	○	○	—
AutoPhone™	—	—	—
Charging contacts	—	—	—
Battery Size	13 / 312	312 / 10	10
Battery door on/off function	●	●	●
Nanocoated housing	—	—	—
e2e wireless™ 3.0	—	—	—
Audio streaming	—	—	—
User controls coupling via e2e	—	—	—
Wireless programming	—	—	—
Instrument configurations			
Flat cover	—	—	—
Volume wheel	○	○	—
Push button	○	○	○
Rocker switch	—	—	—
Color conversion kit	—	—	—
Battery door – direct audio input	—	—	—
Battery door – child lock	—	—	—
Small earhook	—	—	—
Accessories			
miniPocket	○	○	○
CROS Pure	—	—	—
eCharger	—	—	—
easyPocket™	—	—	—
easyTek	—	—	—
TV Transmitter (req. easyTek)	—	—	—
Transmitter (req. easyTek)	—	—	—
VoiceLink™ (req. easyTek)	—	—	—
App			
easyTek App (req. easyTek)	—	—	—
touchControl App™	○	○	○

● available ■■■■■ highest feature performance ○ optional — not available

1) channels

2) handles

3) presets

4) req. bilateral fitting and e2e™ 3.0

5) req. CROS Mic

6) req. bilateral fitting, e2e 3.0™ and single mic instruments

7) steps

8) streaming only, req. easyTek

9) classes

10) iOS™ / Android™

11) req. e2e 3.0

12) req. easyTek & easyTek App or touchControl App

13) req. AutoPhone

14) req. directional microphone

Prompt Click

Technical Data



ITC

CIC

Prompt Click | Features and Accessories

	ITC	CIC
Audiology		
Signal processing (channels) / Gain/MPO (handles)	8 / 4	8 / 4
Hearing programs	4	4
SpeechMaster	—	—
HD Music (presets)	—	—
TwinPhone¹⁾	—	—
EchoShield	—	—
Wireless CROS/BICROS²⁾	—	—
Directionality (channels)	—	—
Narrow Directionality¹⁾	—	—
Directional microphone	—	—
Spatial SpeechFocus¹⁾	—	—
SpeechFocus	—	—
TruEar™	—	—
Frequency compression	—	—
Extended bandwidth	—	—
Feedback cancellation	●	●
eWindScreen binaural¹⁾	—	—
eWindScreen™ (steps)	—	—
Noise Reduction (channels / steps)	—	—
Speech and noise management (steps)	on / off	on / off
SoundSmoothing™ (steps)	—	—
Directional speech enhancement (steps)	—	—
Adaptive streaming volume³⁾	—	—
SoundBrilliance™ ³⁾	—	—
Sound equalizer (classes)	—	—
Spatial Configurator¹⁾	—	—
Span⁴⁾	—	—
Direction⁵⁾	—	—
SoundBalance	—	—
Fitting		
Insitugram	●	●
Learning (classes) / Data logging	— / ●	— / ●
Acclimatization manager	—	—
Tinnitus		
Tinnitus noiser		
Static therapy signal (handles / presets)	—	—
Ocean Waves therapy signal (presets)	—	—

Prompt Click | Features and Accessories

	ITC	CIC
Style Specific Features		
Ingress Protection Rating	—	—
Telecoil	—	—
AutoPhone™	—	—
Charging contacts	—	—
Battery Size	312	10
Battery door on/off function	●	●
Nanocoated housing	—	—
e2e wireless™ 3.0	—	—
Audio streaming	—	—
User controls coupling via e2e	—	—
Wireless programming via ConnexxLink™	—	—
Instrument configurations		
Flat cover	—	—
Volume wheel	—	—
Push button	●	—
Rocker switch	—	—
Color conversion kit	—	—
Battery door – direct audio input	—	—
Battery door – child lock	—	—
Accessories		
miniPocket	○	○
CROS Pure	—	—
eCharger	—	—
easyPocket™	—	—
easyTek	—	—
TV Transmitter (req. easyTek)	—	—
Transmitter (req. easyTek)	—	—
VoiceLink™ (req. easyTek)	—	—
App		
easyTek App (req. easyTek)	—	—
touchControl App	○	○

● available ■■■■■ highest feature performance ○ optional — not available

¹⁾ req. bilateral fitting and e2e™ 3.0

²⁾ req. CROS Pure accessory

³⁾ streaming only, req. easyTek™

⁴⁾ req. easyTek & easyTek App, touchControl App or rocker switch

⁵⁾ req. easyTek & easyTek App or touchControl App